

Strain Gage Adhesive

OTHER ACCESSORIES USED IN AN M-BOND AE-15 INSTALLATION:

- CSM Degreaser or GC-6 Isopropyl Alcohol
- Silicon-Carbide Paper
- M-Prep Conditioner A
- M-Prep Neutralizer 5A
- GSP-1 Gauze Sponges
- CSP-1 Cotton Tip Applicators
- PCT-2M Gage Installation Tape
- HSC Spring Clamp
- GT-14 Pressure Pads and Backup Plates





RoHS

DESCRIPTION

Two-component, 100%-solids epoxy system for generalpurpose stress analysis. Transparent, medium viscosity. Cure time as low as six hours at +125°F (+50°C). Recommended for more critical applications, including transducers. It has a longer pot life than M-Bond AE-10 which allows more time for multiple gage installations.

Elevated-temperature postcure is recommended for maximum stability, and/or tests above room temperature. Highly resistant to moisture and most chemicals, particularly when postcured. For maximum elongation, bonding surface must be roughened. Cryogenic applications require very thin gluelines.

CHARACTERISTICS		
PARAMETER	DETAILS	
OPERATING TEMPERATURE RANGE	Long Term: -452° to +200°F (-269° to +95°C). Transducers: to +175°F (+80°C).	
ELONGATION CAPABILITIES	2% at -320° (-195°C), 10% to 15% at +75°F (+24°C), 15% at +200°F (+95°C).	
SHELF LIFE	Minimum 12 months at +75°F (+24°C); or 18 months at +40°F (+5°C). If crystals form in resin jar, heat to +120°F (+50°C) for 30 minutes. Cool before mixing. Refer to product label for most recent information.	
POT LIFE	1-1/2 hours at +75°F (+24°C).	
CLAMPING PRESSURE	5 to 20 psi (35 to 140 kN/m²).	
CURE REQUIREMENTS*	Recommended Postcure: 2 hours at 25°F (15°C) above maximum operating temperature. Optimum Performance Transducer Postcure: 1 hour at +200°F (+95°C). GLUELINE TEMPERATURE IN °C → Optimum Performance Transducer Postcure: 1 hour at +200°F (+95°C). GLUELINE TEMPERATURE IN °C → Optimum Performance Transducer Postcure: 1 hour at +200°F (+95°C).	

PACKAGING			
KIT	BULK		
6 mixing jars (10 g ea) Resin 1 bottle (15 ml) Curing Agent 15 6 calibrated pipettes 6 stirring rods	200 g Resin 25 g Curing Agent 10 3 calibrated pipettes		

References: Instruction Bulletin B-137, "Strain Gage Applications with M-Bond AE-10, AE-15, and GA-2 Adhesive Systems", included in each kit.



Legal Disclaimer Notice

Vishay Precision Group, Inc.

Disclaimer

ALL PRODUCTS. PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.

Document No.: 63999 Revision: 15-Jul-2014